

REF. : U900012**SPRAY ETCHING MACHINE WITH RINSING, GIROJET R4**

- Working area 200 x 300 mm
- Etching on 1 side or 2 sides
- Rinsing tank included
- Integrated heater
- Strong
- Performant
- Economic & speed
- Welded PVC

Double sided model with rinsing tank and thermostated heater.
Etching time 2 minutes with a new ferric chloride at 30°C.
Compact model, perfect for laboratory.

Technical specifications

Working area	200 x 300 mm
Tank capacity	7,5 liters
Electrical Supply	230V - 50/60 Hz
Net weight	13,30 Kg
Dimensions L x w x H	500 x 270 x 455 mm

Spray etching machine with rinsing, GIROJET R4 - Ref U900012

Set of product for etching machine GIROJET R4 - Ref U800038