

Specifications for BMP71 Label Printer Labels

| | |
|-------------------------------------|---|
| Adhesive | Static Dissipative Permanent Acrylic |
| After Process | Yes, this material will work with this application |
| Application | Circuit Board & Component Identification |
| Approval/Compliance | UL Recognised;CSA Accepted;Meets the requirements of EIA-541 Packaging Material Standards for ESD Sensitive Items; Meets the requirements of ANSI/ESD S541-2008 (between 104 and 1011 ohms) for dissipative ESD packaging materials |
| Article No. | 114792 |
| Board Application | Static Dissipative;Through Hole - Top |
| Brady Material No. | B-473 |
| Material Type | Static Dissipative Polyester |
| Brand | WorkHorse™ Series |
| Colour | White |
| Finish | Gloss |
| Description | Labels for the BMP™71 Label Printer. Please Note: This material is UL & CSA approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use. |
| Max. Characters per Line | 31 |
| Max. Lines of Text | 2 |
| Max. Service Temp. °C | 120 |
| Order Reference | M71-28-473 |
| Printer Compatibility | BMP71 |
| Ribbon Series | M71-R6000HF |
| Shape | Rectangle |
| Size - Height (mm) | 6.35 |
| Size - Width (mm) | 38.10 |
| Additional Information | Static dissipative adhesive & liner |
| Surface Mount Technology SMT | No, this material does not work with this application |

| | |
|--------------------------------|--|
| Through Hole Technology | Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No |
| Total Qty per Pack | 750 Label(s) / Box |
| Vertical Repeat (mm) | 9.53 |
| Industry | Electronics |
| Min. Service Temp. °C | -40 |
| QTY. per Row | 1 |
| Thickness (mm) | 0.09 |