

Product data sheet

Specifications



SMX 304L stainless monobloc enclosure, H1800xW600xD400mm, Scotch Brite® finish.

NSYSMX18640

Main

Range	Spacial
Product name	Spacial SMX
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	1800 mm
Nominal width	600 mm
Nominal depth	400 mm
Product installation	Floor-standing
Device composition	1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 door

Complementary

Body type	Single piece body folded and welded
Door type	Plain
Door opening side	Reversible (120 °)
Number of doors	Front face: 1 door(s)
Lock type	3 points lock, handle with 5 mm double-bar insert
Type of gland plate	Plain
Accessibility for operation	Front
Mounting plate description	Without mounting plate
Material	Body and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Surface finish	Enclosure: Scotch-Brite® brushed Handle: painted
Net weight	85 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 62208
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Product certifications	CAN/CSA 22 UL 508
Environmental characteristic	Corrosive Specific hygiene

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	85.0 kg
Package 1 Height	193.0 cm
Package 1 width	65.0 cm
Package 1 Length	48.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------