



R2000 – One Word only - Efficiency

Hot air gun with 3 step-position, a useful tool for versatile applications.

Ideal for stripping paint, taking off stickers or simply defrosting water pipes, its power of 2000 W together with its 3-step position (60-350-600°C), will contribute to make of this tool your best partner for handy work. Soft grip handle and protection for secured and comfortable usage. It is not only possible to set the temperature at three levels but it is also possible to operate with different air flow rates. It's great design gives a modern look. It's rubber base makes it stable and safe when working in desk bench position. R2000 integrates thermal fuse to work in safe conditions. Accessories (nozzles, shrink tubes..) are available separately.

Product Specifications

- Power : 2000 W
- Temperature : 60-350-600°C
- Airflow : 250-500 L/min
- Working voltage : 220-240V / 50Hz
- Tool weight : 0,8 kg

Features

- High airflow – 3 positions
- Double soft grip handle for high comfort
- Handle protection
- Ergonomic design
- Stable desk bench position rubber based
- 3 temperature settings
- Available in compact and sturdy carton box



Description	Art. No	EAN	Measurements	Outer	Weight
R2000 V21 box version	5001342	4051661031397	285x100x250 mm	5 pcs	1,2 kg



ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY