









7	09 58 001 9901	UIC558-CGM-P-PG21	1
6	09 15 200 6122	Han D M crimp contact 1,0 mm ² Au/HMC	16
5	61 03 000 0044	Cable clamp metal hood (OD 7-10 mm)	1
4	09 67 000 7470	D SUB FE turned contact_AWG24-28_PL1 HMC	8
3	09 14 008 3134	Han Gigabit Cat8, female	1
2	09 58 024 3001	UICIT_8/16_HMC_MI_CRT_0,09-1,5mm ²	1
1	09 58 001 1452	UICIT_H_PL_PG21_RAL1003	1
SI No.	PART NO.	PART NAME	QTY

Note:
1. Dimensions are in mm and only for reference purpose only.
2. Refer data sheet for product specification.

	All rights reserved		Scale 1:1		Free size tol.		Ref. Sub.	
	Department EL PD		Created by 404742	Inspected by 402933	Standardisation	Date 06-Nov-2024	State 40 - Released	
HARTING		Title UICIT_PL 8/16_KIT		Doc-Key / ECM-Nr. DS00235627				
D-32339 Espelkamp		Type TB	Design Number DS00235627	SAP Mat. Number 19580241031		Rev. B	Page 1/1	