



Brand of NTN corporation

## Technical data

# LUBER READY UNIVERSAL + Ready



### MAIN LUBRICANT FEATURES

Type of lubricant	Grease
Consistency	2
Base oil	Mineral
Thickener	Lithium / calcium
Max lubricant service temperature	403,15 °K
Min lubricant service temperature	243,15 °K
Viscosity at 100°C	11.5 cst
Viscosity at 40°C	150 cst

### MAIN GREASER FEATURES

ATEX certification	Oui/Yes
Capacity	0,125 l
Diameter	58 mm
Distribution time	1 to 12 months
Driving type	Electrochemical
Length	117 mm
Mass	0,215 kg
Max pressure	5 bar
Pression maxi	5 bar
Max operating temperature	333,15 °K



## NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

**MAIN GREASER FEATURES**

<b>Min operating temperature</b>	253,15 °K
<b>Type of lubricant</b>	Universal +

