

FFCB 200UKA Easy Fuse Finder Kit

Receiver
FFCB RCV



Transmitter
FFCB TXA



DUAL VOLTAGE

100-130V - CAT III + 200-250V - CAT III



Features as FFCB 100A plus

- Fused Test Lead Set gives easy connection to 13A BS 1363 sockets plus distribution boards and lighting circuits
- All test leads and connectors fully conform to IEC, HSE GS38 and Supply Industry M15/4 standards and recommendations
- Custom case means less chance of leaving units behind on site



IECP UKA



IEC 2PA



TECC 10A

WHAT'S IN THE KIT

Contents		
FFCB TXA	Easy Fuse Finder Transmitter	£45.00
FFCB RCV	Easy Fuse Finder Receiver	£50.00
IEC 2PA	2 pole Fused Test Lead Set	£35.00
IECP UKA	IEC lead to 13 amp plug	Included
FFCBINS	Instruction Manual	Included
TECC 10A	Carrying Case	Included
		£130.00



Battery not supplied. (9V MN 1604 or similar)



ALSO AVAILABLE

FFCB 200EUA Professionals Electricians Kit Euro
Euro Kit features as FFCB 200UK except 13A plug replaced by round pin CEE7/VII Euro plug

Specifications for FFCB 100UKA, FFCB 100EUA, FFCB 200UKA and FFCB 200EUA

For use on 110 -230V 50 - 60Hz Mains supply (including 55-0-55V AC Systems)

Current consumption: <20mA L-N No RCD Trip

Calibration: The microprocessor is self-calibrating, no other form of calibration is necessary

This product is EMC and LVD compliant

