

910.13 SS G1/2B / G1/2 LH-RH union 20...60 bar

Overpressure protector, adjustable

Item number: 9091548

Quantity: 1 pcs.

Order code: 910.13-SS1B4-1ZZ-F71-ZZ 0

Overview: 910.13 SS G1/2B / G1/2 LH-RH union 20...60 bar
Overpressure protector, adjustable
Material body: Stainless steel 1.4571
Connection process side + instrument side: G 1/2 B male + G 1/2 LH-RH union
Material sealing : FPM
Permissible medium temperature: -10...+80°C
Setting range: 20...60 bar
Factory setting, set at: 40 bar

Details: Overpressure protector, adjustable
Specifications according to data sheet: AC 09.04
Special design features: NACE Sour Gas Service
Material body: Stainless steel 1.4571
Material sealing : FPM
Permissible medium temperature: -10...+80°C
Connection process side + instrument side: G 1/2 B male + G 1/2 LH-RH union
Overpressure safety: 1000 bar
Setting range: 20...60 bar
Factory setting, set at: 40 bar