

Han Yellock 30HSM 1xM25 with bulkhead h.



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 300 1211
Specification	Han Yellock 30HSM 1xM25 with bulkhead h.
HARTING eCatalogue	https://harting.com/11123001211

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Surface mounted housing
Description of hood/housing	incl. bulkhead mounted housings

Version

Size	Han-Yellock® 30
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Screw locking
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance
 Since 1945

Material properties

Colour (hood/housing)	RAL 7021 (black grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	522 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140109957
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466