



DCH254M2

18V XR Li-Ion Heavy Duty 3 Mode Quick Change Chuck Dedicated Cordless Hammer

Selling Proposition

- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 24mm
- Rotation stop mode for light chiselling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal
- 4.0Ah 18 Volt Lithium Ion battery, delivers high performance, long life and maximum runtime
- Quick release SDS-Plus toolholder and keyless chuck supplied for easy switching between hammer / rotary hammer and rotary only applications
- Best in class vibration, 6.6m/s² reduces user fatigue and maximises operating periods
- Bright white LED with delay feature improves visibility

Standard Equipment

- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator
- Multi-voltage XR charger
- Multi-position side handle
- Quick release SDS-Plus toolholder
- Quick release 13mm 3 jaw chuck

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 3 Year Limited Warranty
- 1 Year Free Service Contract

Specifications	
Battery	XR Li-Ion
Voltage	18 V
Battery Capacity	N/A Ah
Power Output	400 Watts
No Load Speed	0-1200 rpm
Impact energy (EPTA 05/2009)	2.1 J
Blows per Minute	0-4500 bpm
Tool Holder	SDS-Plus