

## Han 32A-Cover (Plastic)



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 5407
Specification	Han 32A-Cover (Plastic)
HARTING eCatalogue	<a href="https://harting.com/09200325407">https://harting.com/09200325407</a>

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

### Version

Size	32 A
Locking type	Double locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances Potassium 1,1,2,2,3,3,3,4,4,4-nonafluorobutane-1-sulphonate

---

## Specifications and approvals

Approvals DNV GL

## Commercial data

Packaging size	1
Net weight	31.16 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140191792
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467

---