



PRODUCT-DETAILS

EXLB0310

16MM GS-PVC COAT EX COND 10M - BL



General Information

Extended Product Type:	EXLB0310
Product ID:	7TCA297120R0066
EAN:	5011949001107
Catalog Description:	16MM GS-PVC COAT EX COND 10M - BL
Long Description:	Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 16mm, Minimum Bore 12.5mm, Reel Length 10 Meters, Galvanised Steel Core with Flame Retardant PVC Covering, Black
Display Name:	EXLB0310

Additional Information

Product Main Type:	KOPEX-EX FLEXIBLE CABLE PROTECTION
Application:	Connection for Conduit Systems when Oil and Acid Resistance is Needed

Ordering

EAN:	5011949001107
------	---------------

UPC: 786210287379

Technical

Number of Batteries:	0
Color:	Black
Material:	Galvanized Steel Core with Flame Retardant PVC Covering

Environmental

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5011949001107
Package Level 1 Height:	5.9 in 150 mm
Package Level 1 Depth / Length:	12.59 in 320 mm
Package Level 1 Width:	12.59 in 320 mm

Certificates and Declarations

Declaration of Conformity - CE:	9AKK107492A9617
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

External Classifications and Standards

ETIM 8:	EC001179 - Protective metallic hose
ETIM 9:	EC001179 - Protective metallic hose
UNSPSC:	39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

