

Neodymium shallow pot datasheet

Hook Magnet

- Zinc plated body
- 80° max operating temp
- Used in point of sale etc.



Product Information

Product Number	Eclipse Product Number	Pull force (kg)	Dia (mm) D	Height (mm) H	Overall Height (mm) D1	Thread (mm)	Weight (g)	Units Per Pack
1466181	E1030/NEO	2.5	10	4.5	15	M3	4.5	20
1466182	E1031/NEO	6.0	13	4.5	15	M3	7.5	20
1466183	E1032/NEO	9.5	16	4.5	20.5	M4	13.2	20
1466184	E1033/NEO	14	20	6	22	M4	16.5	10
1466185	E1034/NEO	20	25	7	23	M4	34	10
1466186	E1035/NEO	35	32	7	30	M5	48	5

If you have any more questions, require technical assistance and would like a quotation, simply contact us.

www.eclipsemagnetics.com

Eclipse Magnetics Ltd, Atlas Way, Sheffield, S4 7QQ, England
T +44 (0)114 225 0600 F +44 (0)114 225 0525 E info@eclipsemagnetics.com

While every effort has been made to ensure the accuracy of the information in this publication please note that specifications may change without notice.



FM31278