



Sample photo

Order symbol: AB 121609
Product nbr: 7083720
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074003546
EI. number:
 Finland: 3423486
 Electric No. Denmark: 8212003486
 Electric No. Italy: 7311040
 Electric No. Sweden: 7083720

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	160	120	90	Ingress Protection (EN 60529): IP66/IP67
inch:	6.3	4.7	3.5	Impact Resistance (EN 62262): IK07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			Flammability Rating: UL 94 HB
Cover screws material:	Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 650
Cover colour:	RAL 7035 -light grey			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 80 °C			
Temperature °C (continuous):	-40 ... 60 °C			
Temperature °F (short term):	-40 ... 175 °F			
Temperature °F (continuous):	-40 ... 140 °F			

