

Eaton 12BDGHA20

Catalog Number: 12BDGHA20

Eaton Bussmann series medium voltage BS air fuse, 20 A, AC 12 kV, 359 x 50.8 mm, backup, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BDGHA20
	EAN
	5027590431125
UPC	Product Length/Depth
051712240963	359 mm
Product Height	Product Width
50.8 mm	50.8 mm
Product Weight	Compliances
2100 g	BS 2692-1

Product specifications

Resources

Type

Fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

20 A

Fuse indicator

With Striker

Fuse size

51 x 359 mm

Breaking capacity

40 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Fuse shape

Cylindrical

Element

Silver

Pre arc (I2T)

1.6 x 102

Resistance

63.3 ohms

Fuse diameter

51 mm

Interrupt rating

40 kAIC

Construction size

51 x 359 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

BDGH