



ENGLISH

Datasheet RS Pro Metric & Imperial Dial Caliper, Micrometer, Rule Measuring Set

RS Stock No: 841-2527



Specifications:

This set contains a selection of measuring tools most suitable for students and apprentices

Set contents:

Dial Caliper: 150mm

Mechanical Micrometer: 0-25mm

Satin Chrome Rule: 150mm/6"

Order Code	Manufacturers Code	Description
841-2527	50-610-025N	3 Piece Measuring Set



ENGLISH

Datasheet

RS Pro Metric & Imperial Dial Caliper, Micrometer, Rule Measuring Set

Specifications:

Dial Caliper

Hardened stainless steel body

Satin chrome finish

Thumbroll

Depth Rod

Four-way measurement:

Outside

Inside

Step

Depth

White dial face

Range: 150mm

Metric Grads: 0.02mm

Accuracy: ± 0.02 mm

External Jaw Depth: 40mm

Internal Jaw Depth: 18mm

Mechanical Micrometer

Range: 0-25mm

Accuracy conforms to DIN 863

Resolution: Metric 0.01mm

Micro fine graduations for accurate reading

Tungsten carbide measuring faces

Spindle locking lever

Ratchet stop

Non-glare satin chrome barrel and sleeve

Blue baked enamel hammer tone finish

Supplied in fitted case with adjustment tools



ENGLISH

Datasheet

RS Pro Metric & Imperial Dial Caliper, Micrometer, Rule Measuring Set

Specifications:

Steel Rule Metric and Inch Two Sided with Round End

Conform to EEC-Class 1, Ref 73/362/EEC

Manufactured from high quality steel

Fully hardened and tempered

Non-glare satin chrome finish

Graduations etched from precise glass masters for repeated accuracy

Length: 150mm / 6"

Type: Rigid

Width and Thickness: 19 x 0.5mm

Rule Marking: Front Face (inch) 16ths, 32nds, 64ths, 10ths, 20ths, 50ths, 100ths

Rule Marking: Reverse Face Metric) 1.0mm and 0.5mm

Style: 64R

End Style: D End