

FEATURES

- Impedance of 50 ohms
- Strong black and red sheath
- This BNC RF coaxial cable assembly uses RG58/U coaxial cable and UL AWM 1015 18AWG cable
- Length of 1.2 m

RS PRO Coaxial Cable

RS Stock No.: 526-0241



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, comes a high quality and great value cable. Manufactured out of industry-standard components, this flexible 50 Ohm male plug on one end and two colour coded black and red alligator clips the other.

Coaxial type cables are designed to carry signals over long distances and are easy to install.

General Specifications

Coaxial Type	RG58/U
Connector A	Male BNC
Connector B	Crocodile Clip
Terminated/Unterminated	Terminated
Sheath Colour	Black
Applications	Connecting radio transmitters and receivers with their antennas, Computer network (Internet) connections, Feeding satellite signals through to your TV.

Electrical Specifications

Characteristic Impedance	50 Ω
---------------------------------	-------------

Mechanical Specifications

Length	1.2m
Cable Shape	Coaxial

Approvals

Compliance/Certifications	EN61340
Standards Met	UL AWM 1015

