

# Reciprocating Saw LXT®

## DJR187

18V • 0 – 3 000 min<sup>-1</sup> • 32 mm

### Efficient brushless reciprocating saw

An efficient brushless reciprocating saw for spark-free cutting of metal and demolition work for professional use. Two speed settings, stroke length of 32 mm and stroke rate of 0 – 2 800 min<sup>-1</sup> with continuous control from the switch. Quick-release blade attachment.



### Technical specifications

|                                            |                                   |
|--------------------------------------------|-----------------------------------|
| Nominal Battery Voltage                    | 18 V                              |
| Voltage LXT                                | ✓                                 |
| Brushless Motor                            | ✓                                 |
| Strokes per Minute (SPM)                   | 0 - 2300 / 3000 min <sup>-1</sup> |
| Length of Stroke                           | 32 mm                             |
| Max. Cutting Capacity in Wood (90°)        | 255 mm                            |
| Max. Cutting Capacity in Steel Pipe        | 130 mm                            |
| Sound Power Level (L <sub>WA</sub> )       | 95 dB(A)                          |
| Sound Pressure Level (L <sub>pA</sub> )    | 87 dB(A)                          |
| Noise Uncertainty (K Factor)               | 3 dB(A)                           |
| Tool weight with battery                   | 3,4 - 3,8 kg                      |
| Product Dimensions (L x W x H):            | 439 x 83 x 231 mm                 |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion                            |
| Vibration Level, Cutting Boards            | 16,5 m/s <sup>2</sup>             |
| Vibration Uncertainty (K Factor),          | 1,5 m/s <sup>2</sup>              |

### User benefits

- Tool-less blade change and shoe adjustment
- LED light illuminates the work site
- Wide hanging hook, e.g. for scaffolding
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low
- Slim design with rubberised grip for comfort

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing