

Products Low Voltage Products and Systems Industrial Plugs and Sockets Easy & Safe Connectors

General Information

Extended Product Type:	432EC6
Product ID:	2CMA102051R1000
EAN:	7392696020510
Catalog Description:	Industrial Connectors, 3P+N+E, 32 A, 346 ... 415 V
Long Description:	Industrial Connectors, 3P+N+E, IP44, 32 A, 346 ... 415 V

Additional Information

Additional Information:	3P+N+E
Cable Cross-Section:	2.5 ... 6 mm ²
Cable Diameter:	22 mm
Color:	Red
Connection Type:	Screw clamp
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700006C0201
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP44
E-number:	2416188
EAC Certificate:	RU C-CZ.ME77.B.02742
EAN:	7392696020510
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001320 - CEE coupling
Enclosure Material:	Plastic (PA)
Environmental Information:	2CMC700001D0002
Frequency (f):	50 Hz 60 Hz
Gross Weight:	0.3 kg
Housing Material:	Plastic (PA)
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#432EC6
Minimum Order Quantity:	10 piece
Number of Poles:	5
Package Level 1 EAN:	7392696030830
Package Level 1 Gross Weight:	3 kg
Package Level 1 Height:	378 mm
Package Level 1 Length:	182 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	154 mm
Product Main Type:	EC
Product Name:	Industrial Connector
Product Net Depth:	183 mm
Product Net Height:	99 mm
Product Net Length:	183 mm
Product Net Weight:	0.3 kg

Product Net Width:	79 mm
Protection Type:	Splashproof
Rated Current (I_n):	32 A
Rated Voltage (U_r):	200/346 ... 240/415 V
SEMKO Certificate:	1617363
Selling Unit of Measure:	piece
Short Description:	Industrial Connectors, 3P+N+E, 32 A, 346 ... 415 V
Size:	183x79x99
Standards:	IEC 60309-1 IEC 60309-2
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour
RAL Number:	RAL 7012 - Basalt Grey

