

R 15-EG-13,5-AL



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0121
Specification	R 15-EG-13,5-AL
HARTING eCatalogue	https://harting.com/09150000121

Identification

Category	Hoods / Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Straight

Version

Locking type	Screw locking
--------------	---------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	10
Net weight	20.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021617
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405