

6316 // SKIN FLEX 3D CUT C

Cut protection gloves
PPE risk category II



Particularly sensitive
Perfect for working with small parts
Very good tactile sensitivity

18
GAUGE



6316 // SKIN FLEX 3D CUT C



Material:	Special yarn, grey
Coating:	PU, black
Size(s):	6-11
Packaging unit:	100 pair(s)
Certification:	EN ISO 21420, EN 388, OEKO-TEX

NITRAS SKIN FLEX 3D CUT C, cut protection gloves, special yarn (HPPE / polyamide / elastane), grey, PU coating, black (colour code: 1210), partly coated on palm and fingertips, high mechanical resistance, knitted wrist, high cut resistance, perfect dexterity, perfect and innovative fit thanks 3D FIT, unique comfort and protection for the user, 18Gauge, touchscreen capable, for food contact, OEKO-TEX STANDARD 100®, ANSI A3 CUT, very high abrasion resistance, PPE risk category II



Size	6	7	8	9	10	11
Colour coding system						

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Wood processing

Advantages

- + Particularly sensitive
- + Perfect for working with small parts
- + Very good tactile sensitivity



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4X42C	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	X
	Tear resistance	1-4	4
	Puncture resistance	1-4	2
	Blade cut resistance (TDM)	A-F	C
EN ISO 21420:2020 + A1:2024	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	PU on special yarn	black
Index finger and thumb	PU on special yarn	black
Back of the hand	Special yarn	grey
Fingertips	PU on special yarn	black
Cuff / knitted wrist	Special yarn	grey

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
6	4059904223929	4059904223981	0,56 m	0,3 m	0,28 m	4,59 kg	
7	4059904223936	4059904223998	0,56 m	0,3 m	0,28 m	4,99 kg	
8	4059904223943	4059904224001	0,56 m	0,3 m	0,28 m	5,39 kg	
9	4059904223950	4059904224018	0,56 m	0,3 m	0,28 m	5,79 kg	
10	4059904223967	4059904224025	0,56 m	0,3 m	0,28 m	6,29 kg	
11	4059904223974	4059904224032	0,56 m	0,3 m	0,28 m	6,79 kg	

Customs tariff number: 61161020910

Country of origin: China