

FEATURES

- **Sintered Bronze Material:** Provides high strength and wear resistance, ensuring long-lasting performance.
- **Flanged Design:** Facilitates easy installation and alignment, reducing assembly time.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing reliability.
- **Bore Size of 10.02 mm:** Fits standard shafts, offering versatility in application.
- **Outside Diameter of 15.04 mm:** Compact size for use in tight spaces.
- **Width of 20 mm:** Provides stability and support in various applications.

RS PRO 10.02 mm Flanged Plain Bearing

RS Stock No: 528-043



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. Its compact design and robust construction make it ideal for use in machinery where space is limited.

General Specifications

Bore Size	10.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	15.04 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

