

KERN CKE65K0.2

Selbsterklärende Zählwaage mit Laborgenauigkeit, Zählauflösung bis zu 360.000 Punkte



Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	40 h
Operating time (Backlight off):	50 h
Operating time (Backlight on):	25 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-129
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 470 x 190 mm
Gross weight:	7,600 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

Construction

Dimensions housing (WxDxH):	350 x 390 x 120 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	340 x 240 mm

Measuring system

Adjustment options:	External calibration
Linearity:	1 g
Readout [d]:	200 mg
Recommended adjusting weight:	50 kg (E2)
Reproducibility:	400 mg
Resolution:	325000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	65 kg
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height:	1,800 cm
-----------------------	----------

Counting

Counting resolution:	325000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
PRE-TARE function:	yes
Suspended weighing:	Hook

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C