



PRODUCT-DETAILS

N6NY-005C-0-M

CBL CLAMP PLN EDGE BLK .312IN DIA



General Information

Extended Product Type	N6NY-005C-0-M
Product ID	7TAG009970R0099
EAN	5414363034384
Catalog Description	CBL CLAMP PLN EDGE BLK .312IN DIA
Long Description	Plain Edge Cable Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 12.7mm (0.50 Inches), Thickness of 1.52mm (0.06 Inches), Hole Diameter of 5.16mm (0.203 Inches), #10 Screw Mounting with Closed Diameter of 7.92mm (0.312 Inches), Bulk Pack

Ordering

EAN	5414363034384
UPC	728494085661

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	12 in 305 mm
Package Level 1 Height	1.75 in 44 mm
Package Level 1 Depth / Length	15 in 381 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	12.5 in

Package Level 2 Height	318 mm 12 in
Package Level 2 Depth / Length	305 mm 18 in 457 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Mounting Type	#10 Screw
Number of Batteries	0
Product Name	NYLON CABLE CLAMP
Product Type	Plain Edge Cable Clamps
Special Functions	Fully radiused inside edges with size markings in inches and millimeters for easy identification.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	N6NY-005C-0-M
Instructions and Manuals	N6NY-005C-0-M
REACH Declaration	9AKK107992A8792
RoHS Information	9AKK107992A8811

Classifications

ETIM 6	EC000127 - Saddle
ETIM 7	EC000127 - Saddle
UNSPSC	39121702
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5029 >> Nylon Cable Clips

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

