

Features

- **Versatile Installation:** No pre-drilled holes for flexible mounting; optional pre-drilling available for quick setup.
- **Heavy-Duty Durability:** Made from premium natural rubber and styrene butadiene rubber, built to withstand rigorous industrial conditions.
- **Optimized for Industrial Use:** Specifically designed for warehouses, loading docks, and factory production lines.

RS PRO Standard Rubber D-Fender 2m Length x 140mm Width x 152mm Height SBR/NR

Vendor Partcode.: 0688170



RS PRO is our own brand range and brings you a wide range of high-quality, great value products offering you more choice. Trusted by engineers all over the world, every part of every RS PRO product has been rigorously tested against demanding industry standards; they're only given the RS PRO Seal of Approval if we're confident of their exceptional quality, which means you can be confident too.

RS PRO NR/SBR D-Fenders, the ultimate solution for industrial impact protection. These robust rubber bumpers are designed to safeguard warehouses, loading bays, and factory environments from accidental impacts, ensuring long-term durability in high-traffic areas. Available in a wide range of standard sizes, with custom variations upon request, RS PRO D-Fenders provide the perfect fit for your specific needs.

Applications

RS PRO D-Fenders are the ideal choice for:

- **Loading Bays:** Reduces impact damage to dock areas and equipment during loading and unloading.
- **Warehouses:** Shields walls and storage units from forklift and machinery collisions.
- **Factory Production Lines:** Protects sensitive equipment and maintains a smooth operational flow.
- **Parking Facilities:** Acts as a dependable bumper to prevent vehicle damage.

Specifications

Material	SBR/NR
Colour	Black
Length	2010mm
Width	140mm
Height	152mm
Wall Thickness	46mm
Hardness	80ShA
Density (g/cm³)	1.9
Weight (Kg)	62

Approvals

Standards Met	REACH
---------------	-------