



Fuse-link, low voltage, 100 A, AC 690 V, 120 kA, NH00, aM, IEC, dual indicator, live gripping lugs



Part no. NH FUSE 100AMP 690V aM SIZE 00 DUAL IND
Catalog No. 100NHM00B-690

EL-Nummer (Norway) 0001664145

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	100
Rated voltage			AC 690 V
Construction size			NH00
Utilization category			aM
Status indicator			dual indicator
Description			live gripping lugs
Breaking Capacity		kA	120
usable for size/applications			industrial
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2
Optional accessories			fuse-holder SD00-D

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			NH00
Rated current		A	100
Rated voltage		V	690
Voltage type			AC
Rated switching capacity		kA	120
Utilization category			aM (switchgear protection)
Type of fuse status indicator			Combination fuse status indicator
Insulated metal gripping lugs (IMGL)			No