



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
Fw - Under rollers diameter	25 mm
dw - Shaft washer bore diameter	25 mm
D - External diameter	37 mm
D1 - Outer diameter of washer	42 mm
C - Width of bearing, drawn cup or outer ring	30 mm
C1 - Thrust bearing height	11 mm
C2 - Hole location	9,5 mm
rs - Min fillet radius	0,6 mm
Lubrication hole on outer ring	Oui/Yes
k - Hole diameter	2,5 mm
Precision class	P0
Mass	0,125 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	14200000 mN
Ca - Dynamic axial load rating	19600000 mN
C0r - Static load rating	24000000 mN
C0a - Static axial load rating	37000000 mN
N lim - Grease lubrication limit speed	27600 °/s
N lim - Oil lubrication limit speed	39000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K



ABUTMENT	
da min - Min shoulder diameter IR	35 mm
ras max - Max shaft & housing fillet radius	0,6 mm

