

Cordless hot air tool - Professional Line

mobile heat MH3

including rechargeable 5.5Ah Battery and charger
EAN 4007841 068226 (RS 212-1579)



Function description

Mobile heat MH3, the 18 V cordless hot air tool with 2 temperature settings (300°C/500°C). Heats up to 300°C in a maximum of 5 seconds. High-performance, with an airflow rate of up to 200 l/min. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case, with 5,5 Ah CAS rechargeable battery and charger.

Technical specifications

Temperature	300 – 500 °C	Replaceable heating element	No
Airflow rate	200 l/min	Restart protection	No
Motor, type	Brush motor	Thermal cut-out	Yes
Function, life expectancy, motor	500 h	Thermostat	No
Temperature setting	2-stage	Dimensions (L x W x H)	225 x 72 x 204 mm
Temperature display	LED segment display	Rechargeable battery voltage	18 V
Power supply, detail	Rechargeable lithium-ion battery	Mains power supply	18 V
Heating element	Ceramic heating element	Model	Case
Loc function	No	PU1, net weight	0,68 kg
Residual heat indicator	No	Manufacturer's Warranty	1 year
Function, hanger	Yes	PU1, EAN	4007841068226

Accessories

EAN 4007841 068257	Spare CAS battery 18V LiHD
EAN 4007841 068349	CAS Fast Charger ASC 145
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 075569	12-piece hot-air accessory kit