

# M18 ONEPD3-502X

## M18 FUEL™ ONE-KEY™ PERCUSSION DRILL

- Higher power efficiency under load - outstanding torque of 158 Nm
- Extremely compact design of 175 mm length for access into tight spaces
- Connect via Bluetooth® with the ONE-KEY™ app
- Save up to 3 custom settings to the tools memory for fast selection on the jobsite
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality
- Adjustable trigger control for all applications with ONE-KEY™
- Configure to any application choosing optimum tool settings for repeatable precision
- Control speed, torque, start and end speeds, anti-kickback functions and LED
- All metal reversible belt clip to hang your tool quickly and easily
- Flexible battery system: works with all MILWAUKEE® M18™ batteries


**REDLITHIUM™**


No load speed (rpm)	0 - 500/ 0 - 2100
Chuck capacity (mm)	13
Max. drilling wood/ steel/ masonry (mm)	89/ 16/ 16
Max. percussion rate (bpm)	0 - 33,000
Max. torque (Nm)	158
Kit included	2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box
Article Number	4933492801