



ENGLISH

15V, 60W United Kingdom Plug-in SMPSU



The RS Pro Range of Class II 60 watt AC/DC United Kingdom plug-in power supplies provide 60 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications

Features:

- United Kingdom Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved





ENGLISH

Specification	
RS Stock Number	1753329
Input Voltage Range	90-264Vac
Input Frequency Range	50-60Hz
Input Current Rated	1.5A Max
Output Voltage Rating	+15V
Output Current Range	4A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	200mVp-p
Efficiency	87% Min
Over Voltage Protection	8A(100-240Vac)
Over Load Protection	Automatic Recovery
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000Vac / 10mAMax
Leakage Current	0.25mA max
Safety Standard	CE-EMC,CE-LVD
EMI Standard	Meet CE(EN55022)
MTBF	100K Hours
Size mm max.	117mm * 51mm * 33.5mm
Weight	140 g
Regulator Type	Switched Mode Power Supply