




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (13% in 4690948374) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 843477-1
TOOL, EXTRACTION RESET



TE Part # 5-147383-8
80 50/50 HDR SMT.390 W/HD VC


Customers Also Bought



TE Part #207359-1
RECEPT HSG,3 POSN,METRIC



TE Part #1-1623819-1
SBL4 R033 5%



TE Part #58495-1
PRO CRIMPER ASSY MULTIMATE



TE Part #66101-3
III+ SKT,18-16,15AU/FL,LP



TE Part #CAT-C8114-SK1
Single Phase Filters, Corcom SK Series



TE Part #58495-2
PROCRIMPER DIE ASSY MULTIMATE



TE Part #66105-3
III+ SKT,24-20,15AU/FL,LP



TE Part #207360-1
PLUG HSG,3 POSN,METRIC



TE Part #66099-3
III+ PIN,18-16,15AU/FL,LP

Documents

Product Drawings

80 50/50 GRID CABLE RECPT

English

CAD Files

Customer View Model

ENG_CVM_CVM_104893-8_H.2d_dxf.zip

English



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_104893-8_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_104893-8_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English