

TouchNTuff® 92-665 92-670

CHEMICAL & LIQUID PROTECTION

NBR NITRILE


SPLASH

STYLE #	COATING MATERIAL	LINER MATERIAL	GRIP DESIGN	CUFF STYLE	COLOUR	AQL	POWDER-FREE	EN SIZE	LENGTH MM	THICKNESS MM	PACKAGING
92-665	Nitrile	N/A	Textured fingertips	Rolled beaded	Light blue	1.5	Yes	6½-7, 7½-8, 8½-9, 9½-10	300	0.10	100 gloves in a box, 10 boxes in a carton
92-670	Nitrile	N/A	Textured fingertips	Rolled beaded	Light blue	1.5	Yes	6½-7, 7½-8, 8½-9, 9½-10	240	0.10	100 gloves in a box, 10 boxes in a carton



Textured single use nitrile gloves

PRIMARY INDUSTRIES



IDEAL APPLICATIONS

- Laboratory analysis
- Chemical industry
- Emergency services
- Electronics
- Intricate parts handling

DESCRIPTION

- Made from an innovative nitrile compound which offers outstanding chemical and mechanical properties, comfort and dexterity.
- Three times the puncture resistance of latex or PVC disposable. Lighter and cooler, yet safer and more durable; better value for money.
- 100% nitrile; no waxes, silicone or plasticizers.
- Powder-free. No risk of contaminating food with corn starch used to powder gloves.
- Textured finish on fingertips. Improved grip.
- Rolled cuff. Provides added protection at wrist and ensures a secure fit.

REMARKS

- Fit for special purpose



CATEGORY III



Print date: 08-05-2014

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu