

# AF116 ... AF370 3-pole contactors

## Main accessories



1SFC101071V0001

CAL19-11



1SFC101035V0001

VM19



1SFC101041V0001

LT370-30C



1SFC101049V0001

LX140

### Ordering details (1)

For contactors	Auxiliary contacts	Order code	Pkg qty	Weight (1 pce)
				kg

### Side-mounted instantaneous auxiliary contact blocks

AF116 ... AF370	1	1	CAL19-11	2	0.050
	1	1	CAL19-11B	2	0.050

### Mechanical interlock unit

AF116 ... AF370		VM19	1	0.054
AF116 ... AF140 and AF190, AF205		VM140/190	1	0.088
AF190, AF205 and AF265 ... AF370		VM205/265	1	0.090

### Terminal shrouds

AF116 ... AF140, with compression lugs	LT140-30L	2	0.070
AF190, AF205, with cable clamps	LT205-30C	2	0.050
AF190, AF205, with compression lugs	LT205-30L	2	0.220
AF190, AF205, with shorting bar or between contactor and TOL/EOL in DOL-starters	LT205-30Y	1	0.050
AF265 ... AF370, with cable clamps	LT370-30C	2	0.035
AF265 ... AF370, with compression lugs	LT370-30L	2	0.280
AF265 ... AF370, with shorting bar or between contactor and TOL/EOL in DOL-starters	LT370-30Y	1	0.075
AF265 ... AF370, for use with extending cable clamps, ATK300/2 and OZXB4	LT370-30D	1	0.150

For contactors	Dimensions		Order code	Pkg qty	Weight (1 pce)
	hole Ø mm	bar mm			

### Terminal enlargements

AF116...AF140	6.5	13 x 3	LW140	1	0.115
AF190...AF205	10.5	17.5 x 5	LW205	1	0.260
AF265...AF370	10.5	20 x 5	LW370	1	0.340

### Terminal extension

AF116...AF140	6.5	13 x 3	LX140	1	0.072
AF190...AF250	8.5	17.5 x 5	LX205	1	0.180
AF265...AF370	10.5	20 x 5	LX370	1	0.234

(1) For more information, refer to "Accessories" section.

For contactors	Cable range	Order code	Pkg qty	Weight (1 pce)
----------------	-------------	------------	---------	----------------

### Connector terminal lug kits

AF116...AF140	6-250 MCM	ATK185	3	
AF190...AF250	4-400 MCM	ATK300	3	
AF265...AF370	(2) 4-500 MCM	ATK300/2	3	