



Brand of NTN corporation

Technical data

LUBER READY VIB

Ready



MAIN LUBRICANT FEATURES

Type of lubricant	Grease
Consistency	2
Base oil	Semi-synthetic
Thickener	Lithium / calcium
Max lubricant service temperature	413,15 °K
Min lubricant service temperature	253,15 °K
Viscosity at 100°C	25 cst
Viscosity at 40°C	360 cst

MAIN GREASER FEATURES

ATEX certification	Oui/Yes
Capacity	0,125 l
Diameter	58 mm
Distribution time	1 to 12 months
Driving type	Electrochemical
Length	117 mm
Mass	0,215 kg
Max pressure	5 bar
Pression maxi	5 bar
Max operating temperature	333,15 °K



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

MAIN GREASER FEATURES

Min operating temperature	253,15 °K
Type of lubricant	Vib

