



Security Tech Germany

## 37RK/80mm Granit 'Plus' Mechanism Solid Steel Padlocks

- Cathaphoretic coating & rustfree components : Gives 40 years of corrosion protection
- Through hardened steel alloy body & shackle : Resists all attacks
- 14mm removable shackle : CEN grade 5 security
- Ball bearing locking : prevents lever & torsion attacks
- Rekeyable mechanism : Allows locks to be changed to new key
- Keyed to differ (KD) 250,000 key differs, each lock supplied with key code card : Offers numerous keyed alike (KA) or master keyed (MK) options or further locks made up to same key as per card provided



37RK/80 Granit Padlock  
with  
12KS120 Loop Black

Beyond  
CEN Class 5 Security

### 37RK/80 Granit Padlock

This padlock rekeyable as standard

All Granit padlocks endure a  
-40° Freeze & Impact Test

### ABUS Granit Security

All Granit 37/80 padlocks are supplied rekeyable:  
If the original key security is compromised,  
the lock can be reassembled to take a new key.

The Ultimate in Security



ABUS 'Plus' key card  
supplied with all  
37 Granit locks

Illuminated Key



Each Granit Padlock supplied  
with 1 illuminated &  
1 standard Plus key

Keyed Alike & Master  
Keyed versions available  
to special order

37RK/80 Granit Padlock

ABUS UK Product Reference	ABUS Code	Keying	ABUS GPS	 mm	 mm	 mm	 mm	 mm	 mm	Weight gms	Key Blank	
											Reference	Code
37RK/80	20115	KD	10	22	22	14	79	94	39	1139	ABUS Plus	05078