

WSL-L7

Tool trolley workster smartline

with 7 drawers

Code	ETIM
2977311	EC011808
EAN	UNSPSC
4010886947739	56-12-18-02
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
94032080	



Article description

- Body:
- Dimensions: H 1045 x B 870 x T 505 mm
- Working platform with cover made of ABS plastic with front flattening and anti-roll edge, as well as small additional storage compartments
- Manoeuvrable and easy to steer with drive/steer handle
- Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
- Sides rounded off – a minimum of abutting edges
- Body welded, self-supporting and torsionally rigid
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
- Single pull-out stop prevents more than one drawer from being opened, one-hand operation
- Central locking with cylinder clock
- 7 wide drawers (W 640x D 400 mm) fully extending
- Guide rails with ball bearings
- Load capacity per drawer 20 kg
- Sheet steel, corrosion and scratch-resistant, powder-coated
- GEDORE chassis: • Total load capacity 400 kg
- 4 smooth running wheels on ball bearings (swivel castors Ø 125 mm) with thread guard, one with total brake
- Also in case of maximum loads: smooth running, manoeuvrability and track-keeping
- Options:
- Can be equipped with GEDORE tool modules (No. 1500 ES, 1500 CT, 2005 CT, TS-147, TS-190, TS-308)
- Can be individually subdivided with lengthwise and crosswise dividers
- Delivery without tools and accessories

Article information

Contents (Qty of pieces)	1	Number of lengthwise dividers	optionally available
Version/Execution	with single pull-out stop	Number of drawers	7
Net weight [kg]	85 kg	Load capacity per drawer [kg]	20 kg
Total length [mm]	870 mm	Drawer type	5x Type 1, H = 80 mm 2x Type 2, H = 162,5 mm
Total width [mm]	505 mm	Fixed roller diameter (2x)	125
Total height [mm]	1.045 mm	Swivel castor diameter with brakes (2x)	125
Surface	powder-coated	Single pull-out stop	yes
Material	sheet steel	Number of wheels	4
Colour	RAL 5017	Working height	1.045
Dimension (L x W x H)	1.045 mm x 505 mm x	Static load carrying capacity [kg]	400 kg
Number of crosswise dividers	optionally available	RAL colour tone	blue