

Data sheet

Nylon-6 Re-coil Hose

With 1/4" PT male swivel fitting on both end

PRODUCT DESCRIPTION

- Nylon-6 has an excellent set of properties when compared to other materials. It is also very competitively priced in comparison to other types of Nylon.
- Products of excellent cost-value and performance can be produced with Nylon-6, making this material one of the most sought-after for consumer and industrial products.



SPECIFICATION

Material: N6 Polyamide 6

Temperature Range: -10°C ~ 80°C

Working Length: 60% ~ 70% of material length

Article No	Hose ID*OD (mm)	Hose Length (M)	Coil ID (mm)	Working Length (M)	Color	W.P (bar)
700-5712	7.5*10	6 (20ft)	75	3.6 (12ft)	red	18
700-5721	7.5*10	6 (20ft)	75	3.6 (12ft)	blue	18
700-5724	7.5*10	6 (20ft)	75	3.6 (12ft)	black	18

Note:

hose tail 100 mm / 100 mm

with 1/4" PT male swivel fitting and spring on both end.

1 pc / bag

