

FEATURES

- IP44 Rated, 0410185 is IP66 rated
- Wall mountable
- Red and blue colours offered in this range of power connectors
- Voltage ratings of 415V and 230V offered in this range
- Angled socket, allowing a more convenient connection
- All models offered in the range are highly reliable and excellent quality
- Interlocked and RCD (Residual-current device) protected

IP44 Blue Wall Mount 2P+E RCD Industrial Power Connector Socket, Rated At 32.0A, 230.0 V

RS Stock No.: 410-012



Industrial Power Connectors

Product Description

It comes a range of high-quality wall mountable power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Version	With protection appliance
Commercial Series	DOMINO
Pole Format	2P+E
Gender	Female
Body Orientation	Angled
Material	Engineering Plastic
Colour	Blue
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	32A
Voltage Rating	230V
Working Frequency	50Hz; 60Hz
Plug/Socket	Socket
Termination Method	Pre-Wired
RCD Protection	On single outgoing circuit/socket

Mechanical Specifications

Mounting Type	Wall Mount
----------------------	------------

Industrial Power Connectors

Protection Category

IP Rating

IP44

Approvals

Compliance/Certifications

EN61340

