

Nimbus RFID Lock with Scheduled Unlock 3965



Product Description

Say goodbye to locker blocking and open the door to 100% locker availability at the start of each day thanks to the Nimbus RFID with Scheduled Unlock. The feature rich functionality supports up to 50 private mode users at one time and provides a full electronic audit trail for visibility and control.

Enhanced RFID Features

- Multiuser private mode with up to 50 concurrent users – PIN code or RFID card
- Up to 3 Master Users
- Log/Audit file creation – Record the date and time for each multiuser private mode lock event against that user
- Audit file accessible by writing to the RFID card – Audit file read by PC card reader and Nimbus RFID software
- Ability to Clone Lock Settings by programming an RFID card, the unprogrammed lock can read the RFID card to replicate the master settings

Real Time Clock Features

- Functions to set time and date
- Unlock function allowing unlocking at a fixed time every day to avoid user locker blocking
- Set public mode scheduler which provides the ability to set operating times for everyday of the week – also sets RFID scan times
- Auto unlock after 0-999 minutes after the last lock event
- Note: both auto scheduled unlock function and public mode operating times cannot be set at the same time.

Standard Features

- Compatible with ISO14443A RFID standards including Legic-Advant-Protocol and Mifare-Protocols
- **User modes:** Public mode, Private mode, Multiuser mode (Private mode only) or RAS mode
- **Standard finishes:** Black, silver, white powder coat
- **Optional finishes:** Satin or Chrome (MOQ applies)
- **Fitting options:** Surface mount or semi-flush fit fitting (maximum 20mm protrusion)
- **Mounting options:** Vertical and Horizontal (left or right hand fixing, numbers rotated to orientation)
- **Steel Mechanical Override Key:** 2 keys per 50 locks
- **Robust design:** Zinc diecast construction housing
- **Spindle length:** 20mm and 24mm spindle length
- **Lock movement:** Left 90° or Right 90°
- **Cam fixing:** 8mm SQ. with M4 thread
- **Environmental Protection:** IP4X Rated Not for wet areas / applications
- **Temperature Rating:** -8°C to +50 °C

- **Declaration of Conformity:** CE Marked

Options

Product Code	Body Width	Body Height	Body Depth
3965	41	140	24.75