

Professional Cable Reel 320 KU 4200 IP 44, 40 m H07RN-F 3G2,5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use, IP 44.



**MADE IN
GERMANY**



Product number 9232400100
EAN 4007123687725

DESCRIPTION

- Reel body made of special plastic on galvanised support frame.
- 5 splash-proof sockets with earthing contact, with self-closing lids.
- Innovative „cablepilot“ carrying handle for perfect cable routing. Swings on both sides for convenient carrying and hanging.
- With twist handle for convenient retraction.
- With drum brake.
- Category 2 equipment (K2 DGUV 203-005): Use for rough operation with high mechanical, physical and chemical impacts.
- RN cable is approved for harsh building conditions in accordance with VDE 0100 Part 704.
- Overheating protection with indicator light for overheating and overloading.
- With visual readiness indicator.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Plug system socket	Type F (Protective contact)
Cable length	40 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07RN-F 3G2,5	Max. current carrying capacity	16 A
Cable colour	black	Nominal input voltage	230 V
Reel diameter	320 mm	Degree of protection (IP)	IP44
Plug system CEE socket	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	10.3 kg
Weight of product (without packaging)	10.3 kg	Dimension LxWxH (incl. packing)	20.5 cm x 32.5 cm x 41.5 cm
Dimension LxWxH (without packing)	20.5 cm x 32.5 cm x 41.5 cm		

SCOPE OF DELIVERY

Professional Cable reel 320 KU 4200 IP44