

DCLE34035D1-QW

Multi-line laser level 3x360° XR 18V 2Ah Li-Ion - green beams - remote controlled



5035048834633



Product Description:

Working range (diameter) (m): 70 - 100 with cell
Remote control range: 100 m
Accuracy: +/- 3 mm to 10 m
Tripod thread: 3/8" - Magnetic angle clamp holder
IP54

Product features and benefits:

- MAKES YOUR JOB EASIER! Remote control with a range of 100 m to PRECISELY adjust the laser beams horizontally (up to 120°) AND vertically (approx. 9 cm).
- SAFETY +: Electronic fall indicator.
- VERY EFFICIENT: new very high visibility 3x360° green beam diodes. 80 m / 100 m with detection cell.
- VERY PRECISE: possibility to manually adjust the laser left/right/up/down.
- Short press to move a notch. Long press to increase the speed by 3 notches every 2 seconds. PRACTICAL: indicators to check the battery charge level and the use of the remote control.
- ADAPTS TO THE CONDITIONS OF THE CONSTRUCTION SITE: 3 levels of light intensity. Choice of the number of beams.
- ATTACHES ANYWHERE: on 5/8" tripod - On a magnetic stand, with clamp/screw for edge angle. Also Arises directly on the ground (very stable).
- POSSIBILITY TO MAKE CREEPERS with slope adapter. 3-position button: manual slope / automatic leveling / trim block.

Specifications techniques :

- [Imperial] Battery Capacity: 2 Ah

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Laser (x1) Remote Control
- (x1) 2.0 Ah Battery DCB203
- (x1) DCB107 Charger (x1)
- Wall Mount (x1)
- Target (x1) TSTAK
- Box (x1)

DCLE34035D1-QW

Multi-line laser level 3x360° XR 18V 2Ah Li-Ion - green beams - remote controlled



5035048834633

Part of the DCLE34035D1 series

| Ref | ▲ ▼ Title | ▲ ▼ |
|----------------|---|-----|
| DCLE34035D1-QW | Multi-line laser level 3x360° XR 18V 2Ah Li-Ion - green beams - remote controlled | |