

Day/night mini outdoor dome camera

Art. no. TVCC34010

Page 1 of 1

- Compact day/night vision mini outdoor dome camera
- Varied camera installation options – whether indoors or outdoors
- Simple design and high protection class (IP66)
- High detailed resolution, thanks to 600 TVL
- 1 x 20 metre coaxial cable included
- Ideal for extension of TVR30004 or TVR30104

Unobtrusive monitoring indoors or outdoors

The analogue day/night outdoor dome camera is the ideal supplement to the TWR30004 4-channel recorder and the TVR30104 video surveillance kit. It stands out with its plain design and high protection class (IP66), which means it can be used both outdoors and indoors. The camera has integrated IR LEDs for 24/7 use both day and night.

With a high, detailed resolution of 600 TVL, it delivers precise video images for accurate recognition of persons.

Flexible mounting options

Fast and easy installation is guaranteed with the 20 m combination cable and power supply unit provided.

Technical Data:

Dimensions	90 x 59 mm
Connections	Video signal (BNC), power supply (DC)
Image sensor	1/3" DIS
Pixels (effective)	720 (H) x 480 (V) pixel
Electronic shutter	1/25 ~ 1/15.000 sec.
Backlight compensation	Yes
Horizontal angle of view	68,4 °
IR LEDs	12
IR range	10 m
Camera type	Day/night outdoor camera
Max. operating temperature	+ 50 °C
Max. humidity	max. 90 %
Min. operating temperature	- 20 °C

Minimum illumination (color)	0,1 Lux
Minimum illumination (IR)	0 Lux
Lens	3.6 mm, fixed lens mm
Noise reduction	> 52 dB
IP protection class	66
DC voltage supply	12 V
Power consumption	420 mA
Day/night switching	Electromechanical IR-cut filter
TVL	600 TVL
Video system	PAL / NTSC