

**S-20 ; 0...160 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V**

**S-20 ; 0...160 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V**

Item number: 14071149

Quantity: 1 pcs.

Order code: S-20-3-BG516-HSC3K-A-AGGZZZ-ZWZ W1011S20Z-ZZZZ21Z3-SS18LZ2APSZZE-ZZGDZZSAZZZS1

Overview: S-20 ; 0...160 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V  
Pressure transmitter Model S-20  
Non-linearity: 0.25% BFSL  
Overpressure limit: 2 times  
Process connection: G 1/2 B EN 837 ; Sealing: copper  
Pressure port: D 2.5 mm  
Electrical connection: angular connector DIN 175301-803 A mating connector included  
pin assignment el. connection: U+=1, U-=2  
Permissible medium temperature: -30...+100°C  
shock and vibration resistance: 100 g shock, 20 g vibration  
Approvals: cULus  
Test protocol: with test protocol

Details: S-20 ; 0...160 bar gauge; 4...20 mA, 2-wire @ DC 8...35 V  
Pressure transmitter Model S-20  
Non-linearity: 0.25% BFSL  
Overpressure limit: 2 times  
Process connection: G 1/2 B EN 837 ; Sealing: copper  
Pressure port: D 2.5 mm  
Electrical connection: angular connector DIN 175301-803 A mating connector included  
pin assignment el. connection: U+=1, U-=2  
Permissible medium temperature: -30...+100°C  
shock and vibration resistance: 100 g shock, 20 g vibration  
Approvals: cULus  
Test protocol: with test protocol