Datasheet
ECP-12 Series

12w Multi Head Plug In Power Supply

ENGLISH

Features

- Universal input
- No load power consumption
- Compact and light-weight plastic case
- Protections: Short ciruit/ Overload
- Class II power supply (without earth pin)
- Pass LPS
- 1 Year warranty

Model		816-0122	816-0125	816-0129
Input	Input Voltage Range	100-240VAC		
	Input Frequency Range	47Hz to 63Hz		
	No Load Power Consumption	0.3W Max		
	In-Rush Current	50A Max		
	Input Current	0.8A Max		
Output	Output Voltage	+12V	+15V	+24V
	Output Load Range	0.01-1A	0.01-0.8A	0.01-0.5A
Environment	Efficiency	≤83%		
	Working Temperature	0°C-40°C		
	Working Humidity	10%-95%		
Safety	EMI	EN55022 (EN61000-3-2, EN61000-3-3)		
	EMC	EN55024 (IEC61000-4-2, IEC61000-4-3, IEC61000-4-4, IEC61000-4-5)		
Dimensions	Size	101x 52x 36mm		

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.