

Lawn Mower LXT®

DLM330

18V • 330 mm • 30 L

LXT® battery powered Lawn Mower with grass box for small gardens.

DLM330 is optimal in places where you need the ability to turn in small radius. The Plastic cutting deck allows for lightweight design to increase maneuverability in turns, preparation, storage and more. 3 in 1 (Cutting / Collecting / Mulching) usage.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	4300 min ⁻¹
Cutting height positions	8
Width of Mowing Deck	33 cm
Mowing Height	20 - 75 mm
Rear Wheel Diameter	18 cm
Front Wheel Diameter	14 cm
Collecting Box Capacity	30 L
Cumulative	✓
Bio cutting	✓
RPM (Normal mode)	4300 min ⁻¹
Actual mowing area 4.0 Ah	270 m ²
Continuous Use 18V / 4.0 Ah Battery	14 min
Sound Power Level (L _{WA})	89 dB(A)

User benefits

- Soft start for smooth start-ups
- Low noise level suitable for use in residential areas and public spaces
- Compact storage of grass catcher allows for space-saving vertical storage
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating
- 2-tooth blade for both cutting and mulching
- 3 in 1 (Mowing / Grass collecting / Mulching)
- Plastic cutting deck allows for lightweight design to increase manoeuvrability in turns, preparation, storage and more

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing