

PC 7656 base



Sample image

Order symbol : PC 7656 base

Product nr : 6530909

Description : Base, PC

EAN : 6418074078865

El. number :

- Finland : 3424848
- Denmark : 8212049990
- Sweden : 2507811

Dimensions :	Height	Width	Depth
mm :	760	560	150
inch :	29.92	22.05	5.91

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C