

Datasheet

RS Pro 50 Ω Straight Cable Mount MMCX Connector, Plug, Crimp Termination, 0 to 6GHz, RG178/U

RS Stock No: **655-9996**



Product Details

RS Pro cable mount MMCX connector plug is suitable for operating frequencies ranging from 0 - 6 GHz. It is designed for 50 Ω impedance applications. This straight connector plug offers crimp termination and includes gold plated brass body and contacts for superior connectivity. It is compatible with RG178/U type cable. The snap on mechanism gives flexibility in PCB layouts by allowing for 360° rotation.

Features and Benefits

- DC to 6GHz frequency range
- Available in cable, panel and PCB mount versions
- Low RF leakage

Specifications:

Body Orientation	Straight
Body Plating	Gold
Cable Type	RG178/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 6 GHz
Size	Micro Miniature
Termination Method	Crimp
Dimensions	11.7 x 4.5 mm
Operating Temperature Range	-55 to +165°C
Voltage Rating	170 V