

PRODUCT-DETAILS

TC1112

6 BUNDLE MNTG STRIP 9.9X.6IN NAT NY



General Information

Extended Product Type	TC1112
Product ID	7TAG009910R0077
EAN	5414363057994
Catalog Description	6 BUNDLE MNTG STRIP 9.9X.6IN NAT NY
Long Description	Multiple Bundle Mounting Strip, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 252mm (9.9 Inches), Width of 15.87mm (0.625 Inch), Thickness of 5.15mm (0.203 Inch), Two-Screw Mounting Method, #6 Screw, Maximum Tie Width 7.64mm (0.301 Inch)

Ordering

EAN	5414363057994
UPC	786210823249

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	5.3 in 135 mm
Package Level 2 Height	7 in 178 mm
Package Level 2 Depth / Length	12.8 in 325 mm

Additional Information

Brand / Label	Ty-Rap
Cable Size	0.301 in 7.64 mm
Color	Natural
Effective Date	19731120
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Multiple Bundle Mounting Strip
Special Functions	These nylon mounting strips for parallel installation of wire bundles can accommodate up to six closely spaced bundles.
Standards	UL E49405

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC1112
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC1112
REACH Declaration	9AKK107992A8796
RoHS Information	9AKK107992A8808

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

