

Part Number : [190740007](#)

Product Description : Krimptite Star Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5)

Series Number : 19074

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : SRA-129-10



Documents & Resources

Drawings

[190740007_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Star Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal
UPC	800755072723

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.436/g
Packaging Type	Bag
Stud Size	10 (M5)

Wire Size (AWG)	18, 20, 22
-----------------	------------

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640031200</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640071200</u>

This document was generated on Sep 23, 2025