



Part Number : [2041020419](#)
Product Description : VersaBlade Multi-Module
Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural,
Glow-Wire Capable
Series Number : 204102
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[2041020419_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)

[2041020609-001.pdf](#)

[2041020000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	204102
Description	VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	193264280223

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None

Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	3.750/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm, 8.50mm
Pitch - Termination Interface	8.00mm, 8.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>2041020429</u>
VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable	<u>2041020609</u>

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 2 Circuits, Red	<u>1040810282</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm Pitch, 2 Circuits, Natural	<u>359650290</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm Pitch, 2 Circuits, Red	<u>359650292</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.00mm	<u>359650293</u>

Pitch, 2 Circuits, Yellow	
VersaBlade Terminal Position Assurance (TPA) Retainer, Upper Type, 8.50mm Pitch, 3 Circuits, Red	<u>495470392</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, Lower Type, 8.50mm Pitch, 3 Circuits, Natural	<u>495480390</u>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<u>2270288400</u>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<u>2270298400</u>
VersaBlade Male Crimp Terminals	<u>35745</u>
VersaBlade Female Crimp Terminals	<u>35746</u>